

Technical Data Sheet

ANTI-STATIC WIPES

Product Code:	BDPBASW
Revision Date:	01-09-2021
Revision Number:	01

Company:	PPG Industries (UK) Limited
Address:	Needham Road, Stowmarket, Suffolk IP14 2AD U.K.
Telephone:	0044 (0) 1449 773338
Email:	enquiries@ppg.com

Bodyline Anti Static wipes are an innovative design that removes the static charge that is significantly found on plastic components.

Features:

- 25 individual lint free wipes in a resalable pouch to stop the wipes drying out and becoming contaminated.
- The Anti-Static Wipe is impregnated with a special blend of chemicals, removes the static charge prior to the primer / paint application of raw plastic components.
- This should be the last operation before the application of any paint materials. Reducing dirt ingress in the paint film, reducing polishing time and reworks.

Application:

Remove individual wipes from the pouch; reseal the pouch to stop contamination and the product drying out.

Wipe the cloth over the plastic part to remove any static build up that will attract dust and dirt particles. This should be carried out just prior to primer / paint application. Test on a small area first to ensure compatibility. Always wear the correct PPE for the task.

Storage:

Keep the container tightly closed in a dry place. Keep from all sources of ignition, heat and direct sunlight – do not smoke. Highly Flammable.

Please refer to MSDS sheet for full Health and Safety Information.

This data sheet is compiled to be of assistance but without guarantee. Users are responsible for safe working practices. Final determination of suitability of any material is the sole responsibility of the user.