

Technical Data Sheet

AC GEL Activator Aerosol

Product Code:	BACGA
Revision Date:	25/08/2021
Revision Number:	01
Company:	PPG Industries (UK) Limited
Address:	Needham Road, Stowmarket, Suffolk IP14 2AD U.K.
Telephone:	0044 (0) 1449 773338
Email:	enquiries@ppg.com

Bodyline AC Gel Activator Aerosol is a transparent, colourless, solvent base activator to speed up the through curing of Bodyline AC Gel adhesive.

FEATURES:

- Cures AC Gel instantly when applied over the bonded area after the application of AC gel.
- Ideal for bonding small to medium-size parts
- Excellent adhesion to most substrates
- For best performance, bond surfaces should be clean and free from grease.
- Excess adhesive can be dissolved with general cleaning solvents, nitromethane or acetone.

Application.

- Shake can well before applying.
- Apply light to medium coat across bonded area after application of AC Gel adhesive.
- Use in a well ventilated space.
- Avoid inhalation of vapours
- Avoid contact with the skin and eyes. Always wear the correct PPE for the task.
- Keep away from sources of ignition, electrostatic charging. Do not smoke. Highly flammable.

PACKAGING:

- Bodyline AC Gel Activator Aerosol is packed in a 150ml handy use Aerosol.

SHELF LIFE AND STORAGE:

- Bodyline AC Gel Activator Aerosol should be stored out of direct sunlight and temperature over 50oC.
- Store in a well ventilated place. Ideally not in stairwells or gangways.
- Keep cool.

TECHNICAL DATA:

- For further technical information, please see the corresponding MSDS.

This data sheet is compiled to be of assistance but without guarantee. Users are responsible for safe working practices. Final determination of suitability of any material is the sole responsibility of the user.